





The Quadraflo® Standard design oxy-fuel burner combines high turndown with flame adjustability. All combustion occurs off the burner's hot-face and the adjustment provides a means to increase flame stiffness while still maintaining low momentum flame.

Model # QS001G000 Oxygen/Nat Gas Burner



QS001G000 at 1 MMBtu/hr Low Momemtum Setting



QS001G000 at 1 MMBtu/hr High Momemtum Setting

TYPICAL QUADRAFLO® STANDARD SIZES				
MODEL #	NOMINAL RANGE		MAXIMUM RANGE	
	MMBtu/Hr	KW	MMBtu/Hr	MW
QSD50G000	0.5	150	0.25 – 1.0	0.08 – 0.3
QSD75G000	0.75	225	0.38 – 1.5	0.11 – 0.45
QS001G000	1.0	300	0.5 – 2.0	0.15 – 0.6
QS002G000	2.0	600	1.0 – 4.0	0.3 – 1.2
QS004G000	4.0	1200	2.0 – 8.0	0.6 – 2.4